



72217268D

Capacity	L	L1	L2	H		H1		H2	H3
				min	max	min	max		
110kg–1.1t [250lb–2500lb]	ø50 [ø1.97]	101.6 [4.00]	42.5 [1.67]	67.2 [2.65]	70.4 [2.77]	37.0 [1.46]	40.2 [1.58]	24.2 [0.95]	9 [0.35]
2.2t [5000lb]	ø50 [ø1.97]	101.6 [4.00]	42.5 [1.67]	68.0 [2.68]	71.2 [2.80]	31.4 [1.24]	34.6 [1.36]	24.2 [0.95]	9 [0.35]
4.4t [10000lb]	ø70 [ø2.76]	133.4 [5.25]	52.5 [2.07]	93.5 [3.68]	96.7 [3.81]	50.7 [2.00]	53.9 [2.12]	38.5 [1.52]	17 [0.67]



NOTES:

1. Dimensions are in mm[inches].

[illegible]